

Fast GC Technology

Simple - Rugged - Cost Effective

Field Proven Applications

Fast Oven Cool-Down

***Fast Temperature
Programming***



K'(PRIME) TECHNOLOGIES INC.

Unit 105, 90 Freeport Blvd. NE, Calgary, AB T3J 5J9

Tel: (403) 226-5897 Fax: (403) 226-5738

Toll Free: (866) KPRIME-T

info@kprime.net www.kprime.net

GC Chaser - Fast Oven Cool-Down

Simple - Rugged - Field Proven

The GC Chaser by Zip Scientific is a Fast Oven Cool-Down device that increases sample throughput and productivity. It features a simple rugged design that seamlessly integrates into existing GCs.

Cool-down times are reduced by augmenting normal oven ventilation, therefore, no liquid coolants or consumables are required. Methods do not need to be re-validated because the time savings are not gained during the separation.

There is no operating software and the system is completely and automatically synchronized with the GC oven. It can be mounted behind the GC or placed nearby and connected with flexible aluminum ductwork.

